
BAUSCH' & LOMB

20-60x80mm **ELITE**® **Spotting Scope**

Model # 61-0080



This photograph is a guide to the nomenclature and location of the ELITE® Spotting Scope parts mentioned through this text.

Congratulations on your purchase of a Bausch & Lomb® **ELITE® Spotting Scope!**

- The 80mm ELITE® is one of the finest, most versatile prismatic spotting scopes in the world.
- The 80mm ELITE® with ED Glass (Extra Low Dispersion Glass) provides dramatic improvement in color correction with increased contrast
- The 80mm ELITE® is fully multi-coated, providing increased light transmission.
- The 80mm ELITE® contains a waterproof body.
- The 80mm ELITE® comes with a rugged carrying case that can remain on the spotting scope during viewing.
- The 80mm ELITE® is constructed of the finest materials and assembled by highly skilled craftsmen to the highest quality standards.

MOUNTING

The ELITE® Spotting Scope tripod mount provides a convenient means of fastening to any tripod, car window mount or other stable platform. For best results, mount your ELITE® Spotting Scope on a firm support to prevent any movement of the spotting scope. Movement will make the viewed scene appear to vibrate at high magnification. A firm mount will also help you to locate, track and keep objects in the field of view.

ZOOM EYEPIECE

Align the white dot on the front of the eyepiece with the peep sight on the spotting scope body. Insert the eyepiece and turn clockwise until the white eyepiece dot and the peep sight are aligned.

FOCUSING

The ELITE® Spotting Scope will focus from 16 feet to infinity at any power. Rotate the focus knob until you see a precise defined image. The depth of field (the distance over which the image is seen in sharp focus) and the field of view are greatest at lower powers. With the zoom eyepiece, if the initial focusing is done at low power, you may find that additional focus adjustment is required as power is increased.

SIGHTING

Your ELITE® Spotting Scope is equipped with a "peep sight". Look into the rear aperture located just above the eyepiece. Center the object of interest in the field of view and look through the eyepiece. Minimum adjustment will be required to center the object when viewed through the eyepiece.

USE WITH EYEGLASSES

The ELITE® eyepiece is designed to provide you with the longest practical eye relief possible. (Eye relief if the distance from the eye to the eyepiece at which a full field of view is seen.) This provides you with the same field of view with or without eyeglasses. The ELITE® eyepiece is equipped with a rubber eyeguard to eliminate the possibility of scratching plastic eyeglass lenses.

CHANGING POWER

The variable power zoom eyepiece provides a 20x to 60x power range. To change the magnification grasp the eyepiece body and rotate the Power Change Ring to the desired power as indicated by the Magnification Ring. As you zoom from low power to high power under low light conditions, you may notice a decrease in the image brightness. This is normal. As magnification is increased, the amount of light transmitted to your eye, image brightness is decreased proportionately.

SPECIFICATIONS

Field of View (@ 1000 yds.): 98' @ 20x 50' @ 60x Exit Pupil: 4.1mm @ 20x 1.4mm @ 60x Eye Relief: 15.5 @ 20x 16.5 @ 60x

LIFETIME LIMITED WARRANTY

Your Bausch & Lomb® spotting scope is warranted to be free of defects in materials and workmanship for the lifetime of the original owner. The Lifetime Limited Warranty is an expression of our confidence in the materials and mechanical workmanship of our products and is your assurance of a lifetime of dependable service. In the event of a defect under this warranty, we will, at our option, repair or replace the product, provided that you return the product postage prepaid. This warranty does not cover damages caused by misuse or improper handling, installation or maintenance of the product.

> Any return made under this warranty must be accompanied by the items listed below:

- 1) A check in the amount of \$10.00 to cover the cost of handling
- 2) Name and address for product return
 3) An explanation of the defect
- 4) Product should be well packed in a sturdy outside shipping carton to prevent damage in transit and return postage prepaid to the address listed below:

IN U.S.A. Send To: **Bushnell Performance Optics** 8500 Marshall Drive Lenexa, Kansas 66214

IN CANADA Send To: Bushnell Performance Optics 25A East Pearce Street, Unit 1 Richmond Hill, Ontario L4B 2M9

For products purchased outside the United States and Canada please contact your local dealer for applicable warranty information. This warranty gives you specific legal rights. You may have other rights which vary from country to country.

Bausch & Lomb® is a registered trademark of and used under license from Bausch & Lomb Incorporated. ©2001 Bushnell Performance Optics

For more information on tripods, car window mount and other Bausch & Lomb® and Bushnell® Sports Optics Visit Our Website at www.bushnell.com

Bausch & Lomb is a registered trademark of and used under license from Bausch & Lomb Incorporated