

CHANNEL VISION Limited Warranty

Channel Vision Technology will repair or replace any defect in material or workmanship which occurs during normal use of this product with new or rebuilt parts, free of charge in the USA, for two years from the date of original purchase. This is a no hassle warranty with no mail in warranty card needed. This warranty does not cover damages in shipment, failures caused by other products not supplied by Channel Vision Technology, or failures due to accident, misuse, abuse, or alteration of the equipment. This warranty is extended only to the original purchaser, and a purchase receipt, invoice, or other proof of original purchase date will be required before warranty repairs are provided.

Mail in service can be obtained during the warranty period by calling (800) 840-0288 toll free. A Return Authorization number must be obtained in advance and can be marked on the outside of the shipping carton.

This warranty gives you specific legal rights and you may have other rights (which vary from state to state). If a problem with this product develops during or after the warranty period, please contact Channel Vision Technology, your dealer or any factory-authorized service center.

P-0321

Affinity"

Model P-0321

CHANNEL VISION"

0

IR Out

0

Input from

CATV

500-167 rev A1

Using the IR-4101 & P-0321

Digital CATV Box


TV set

400000

Input from

Modulator


How IR repeating works



Be sure the emitter is attached directly over the component's IR receiver. To locate the IR receiver, shine a flashlight into the unit and look for the

sensor. Specifications: (typical) 8 - 12 VDC **Voltage Requirements:** IR Freq. range supported: 30 kHz - 60 kHz IR pickup range: 40 ft. @ 38kHz, 25 ft. @ 56kHz IR receiver head dimensions: 0.65" x 0.35" x 0.25" Color: Black CATV - Selects the CATV input on the P-0321 Specifications subject to change without notice. MOD - Selects the modulator input on the P-0321

The IR-4101 includes these items:




- Plasma Proof IR receiver
- Compatible with: IR-4000, E2200IR, E3200IR, E4200IR, & P-0321
- Versatile mounting accessaries: Install as Very small receiver In-cabinet tube type receiver


Unobtrusive desktop type receiver

Basic IR-on-coax Setup


A basic IR system, like the one shown below, is often used when an audio/video signal is distributed to a remote TV location using the RF output of the device. The IR-4101 is located near the TV, allowing IR signals to be detected, and the IR-4000 is located near the audio/video source, providing an IR emitter output.




Using the IR-4101 with an E-series IR modulator



Mounting the IR receiver: Option 1 - Using the holster



Mounting the IR receiver: Option 2 - Using the hole mount



Mounting the IR receiver: Option 3 - Using the tabletop mount

